

ミガキ材フラットバー 規格対応表

- サイズ：全長(X) 10≦X≦500
- 納期：標準 3 日日出荷、最短 1 日日出荷
(表面処理あり：標準 5 日日出荷。最短 3 日日出荷)
- 加工：面取り、穴形状のみ対応。
※ポケット形状はフラットバー以外の材質をご利用ください。

SS400-D		Y寸																			
冷間引抜き																					
Z寸	5				16	19		22	25			32	38		44		50				
	6				16	19		22	25	28		32	38	40	44	45	50	60	65	75	90
	8				16	19		22	25		30	32	38				50				
	9				16	19		22	25			32	38		44	45	50	60	65	75	90
	10	10		15	16		20	22	25		30	32	38	40			50	60	65	75	90
	12		12		16	19	20	22	25			32	38		44	45	50	60	65	75	90
	16				16	19	20	22	25			32	38		44	45	50	60	65	75	90
	19					19		22	25			32	38		44	45	50	60	65	75	90
	22							22	25			32	38		44		50	60	65	75	90
	25								25			32	38		44	45	50	60	65	75	90
	30									30							50		65	75	100

S45C-D		Y寸															
冷間引抜き																	
Z寸	5		16	19	22	25		32									
	6		16	19	22	25		32	38	44	50	60	65	75	90	100	125
	9		16	19	22	25		32	38	44	50	60	65	75	90	100	125
	12	12	16	19	22	25		32	38	44	50	60	65	75	90	100	125
	16		16	19	22	25		32	38	44	50	60	65	75	90	100	125
	19			19	22	25		32	38	44	50	60	65	75	90	100	125
	22				22	25		32	38	44	50		65	75		100	125
	25					25		32	38	44	50	60	65	75	90	100	125
	30						30				50		65	75		100	125

SUS304-D		Y寸																			
冷間引抜き																					
Z寸	5			15	16	19	20	22	25	30	32	35	38	40		50	60	65	75	90	100
	6			15	16	19	20	22	25	30	32	35	38	40	45	50	60	65	75	90	100
	8				16						32		38			50					
	9			15	16	19	20	22	25		32		38	40		50	60	65	75	90	100
	10	10		15		19	20		25	30	32		38	40		50		65	75		100
	12		12		16	19	20		25	30	32		38	40		50		65	75	90	100
	16				16	19	20		25		32		38	40		50		65	75		100
	19					19			25		32		38			50		65	75		100
	22							22			32		38			50		65	75		100
	25								25		32		38			50		65	75		100
	30									30						50		65	75		100

A6063S		Y寸									
押出材											
Z寸	5			15	20		30	40	50	60	100
	6			15	20		30	40	50	60	100
	8			15	20		30	40	50	60	100
	10	10		15	20		30	40	50	60	100
	12		12	15	20		30	40	50	60	100
	15			15	20		30	40	50	60	100
	20				20		30	40	50	60	100
	25					25	30	40	50	60	100
	30						30	40	50	60	100

